APHP High Pressure Unreinforced Silicone Tubing

Translucent; Platinum Cured



Available as mini and standard Tri-Clamp® ends

call for details!

dvantaSil High Pressure silicone tubing is a high quality, cost effective solution designed for increased flow rates to reduce your processing time. AdvantaSil High Pressure is the optimal choice for Single-Use applications such as TFF, virus filtration, inline integrity testing of filtration assemblies, and high volume fluid transfer.

AdvantaSil High Pressure tubing has undergone extensive physical, chemical and biological testing and meets USP Class VI, FDA CFR 177.2600, ISO 10993, European Pharmacopoeia 3.1.9 and other standards. Full BPOG standardized extractables test protocol has been performed by a fully-accredited, third-party test lab.



ww.advantapure.com

KEY FEATURES

- Allows for processing at higher flow rates
- Full vacuum capabilities on most sizes
- Flexible and translucent yet durable
- Eliminates particulate shedding that can occur when cutting braid reinforced hose
- Certified free of animal-derived ingredients
- General temperature range: -65°F (-53.9°C) to 400°F (204.4°C)
- Resists temperature extremes, compression set, chemical attack, ozone, radiation, moisture and environmental exposure
- Sterilizable by autoclave or gamma irradiation
- Available with validated sterility assurance of 10-6 via gamma irradiation per ISO 11137 method VDmax 25
- Documented lot traceable with identification on packaging
- Documented quality control per ISO 9001:2015

Complete validation package available on request

Full BPOG standardized extractables test results available on request



APHP requires proper cutting techniques for optimal performance. See the instruction video at http://www.advantapure.com/high-pressure-silicone-tubing.htm.





SPECIFICATIONS

Product Number		ninal D. (mm)	(in.)	all (mm)	(in.)).D. (mm)		end adius (mm)	Standard Available Length (ft.)
APHP-0125-0250	.125	3.18	.063	1.60	.250	6.35	.375	9.5	50
APHP-0250-0375	.250	6.35	.063	1.60	.375	9.52	1	25	50
APHP-0375-0625	.375	9.52	.125	3.18	.625	15.88	1.2	30	50
APHP-0500-0750	.500	12.70	.125	3.18	.750	19.05	1.8	46	50
APHP-0750-1000	.750	19.05	.125	3.18	1.000	25.40	2.1	53	50
APHP-1000-1375	1.000	25.40	.188	4.77	1.375	34.93	4.1	104	50

Product Number		Pressure Treated (bar)	Recommended Working Pressure <u>based on 3:1</u>		Burst Pressure Gamma Irradiated 45 kGy		Recommended Working Pressure based on 3:1		Vacuum Capability (in./Hg)
			safety factor		(psi)	(bar)	safety factor		C
			Non-Treated		(Gamma Irradiated, 45 k		Gy
			(psi)	(bar)			(psi)	(bar)	
APHP-0125-0250	CF	CF	CF	CF	CF	CF	CF	CF	>29.5
APHP-0250-0375	125	8.6	42	2.9	144	9.9	48	3.3	>29.5
APHP-0375-0625	177	12.2	59	4.1	211	14.5	70	4.8	>29.5
APHP-0500-0750	140	9.7	47	3.2	157	10.8	52	3.6	>29.5
APHP-0750-1000	109	7.5	36	2.5	123	8.5	41	2.8	>29.5
APHP-1000-1375	115	7.9	38	2.6	131	9	44	3	>29.5

Sold by standard coil length of 50 ft. Add length suffix code "L" to product number when ordering. Example: 50 ft. of .250 in. I.D. x .375 in. O.D. tubing is product number APHP-0250-0375L.

Non-listed sizes and custom lengths are available by special order.

Coils are supplied double bagged in heat-sealed polybags and bulk packed.

Contact your AdvantaPure Sales Representative regarding any special product or packaging needs.

Recommended working pressures are calculated from burst testing using a 3:1 safety factor. Testing was performed at ambient temperature. Application testing is recommended.

CF = Consult factory

APHP requires proper cutting techniques for optimal performance. See the instruction video at http://www.advantapure.com/high-pressure-silicone-tubing.htm.

Address: NewAge Industries AdvantaPure®

145 James Way

Southampton, PA 18966 U.S.A.

Toll Free Phone: 888-755-4370 Phone: 215-526-2151 888-258-4293 Toll Free Fax: 215-526-2167 Fax:

Web Site: www.advantapure.com E-mail: sales@advantapure.com





DISTRIBUTED BY:







